


NOTE:

- 1.OPEN/SHORT/INTERMITTENCE:100%.
- 2.CONDUCTIVE RESISTANCE:2Ω (MAX)
- 3.RoHS & REACH Compliant

Pin OUT



NO.	MATERIAL	DESCRIPTION	QTY.	UNIT
④	MOLDED	45P BLACK PVC		G
③	CONNECTOR	3.5MM PANEL MOUNT FEMALE NICKEL PLATED	1	PCS
②	CONNECTOR	3.5MM NORMAL MALE NICKEL PLATED	1	PCS
①	CABLE	(7*0.12BC*2C+SPIRAL 28*0.10BC) PVC OD:4.0	L	MM

Ltemref	Quantity	Title/Name,designation,material,dimension etc	Article No./Reference
Designed by ALVIN	Checked by HELEN	Approved by - date 11-02-2020	File name Date 11-02-2020
ANGLE:		3.5mm Panel Mount Female/Normal Male 1.0M	
UNIT:MM		AV28710 PSG3305	Edition 1 Sheet 1/1