

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ End Sections

General Information

Extended Product Type:	FEM62
Product ID:	1SNA114994R0700
EAN:	3472591149944
Catalog Description:	FEM62 End Sections Grey
Long Description:	FEM62 - End Sections - Grey - 3mm Spacing.

Ordering

Color:	Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	2.4 g
----------------------------	-------

Technical

Spacing:	3 mm
Function:	End Sections
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	M4/6.SB M4/6.SNB M4/6.SNBT

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225002C1007
Environmental Information:	1SND220090E1000
RoHS Information:	1SND230478F0202

Classifications

Object Classification Code:	X
------------------------------------	---

E-nummer:	2925633
ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	125 mm
Package Level 1 Depth / Length:	170 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.048 kg
Package Level 1 EAN:	3472591149944
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	48000 piece
Product Packing Type:	Bag

