



Main

Range of product	TeSys
Device short name	GV2DM
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 1
Poles description	3P
Utilisation category	AC-3
Motor power kW	9 kW at 440 V AC 50/60 Hz 9 kW at 500 V AC 50/60 Hz 7.5 kW at 400/415 V AC 50/60 Hz 7.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	223 A

Complementary

Device composition	1 motor circuit breaker type GV2ME 1 3-pole contactor 1 combination block GV2AF3
Thermal protection adjustment range	13...18 A
Rated breaking capacity	Iq 15 kA at 400/415 V conforming to IEC 60947-4-1 Iq 6 kA at 500 V conforming to IEC 60947-4-1 Iq 8 kA at 440 V conforming to IEC 60947-4-1
Net weight	0.606 kg
Height	176.4 mm
Width	45 mm
Depth	99.6 mm

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------