



Main

Range of product	TeSys
Device short name	GV2DP
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 2
Poles description	3P
Utilisation category	AC-3
Motor power kW	15 kW at 400/415 V AC 50/60 Hz 15 kW at 440 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	416 A

Complementary

Device composition	1 combination block GV2AF3 1 motor circuit breaker type GV2P 1 3-pole contactor
Thermal protection adjustment range	24...32 A
Rated breaking capacity	Iq 10 kA at 500 V conforming to IEC 60947-4-1 Iq 20 kA at 440 V conforming to IEC 60947-4-1 Iq 50 kA at 400/415 V conforming to IEC 60947-4-1
Net weight	0.741 kg
Height	186.8 mm
Width	45 mm
Depth	111.9 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------