



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1M
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Contacteur Earth terminal Neutral terminal Thermal overload relay
Thermal protection adjustment range	3.7...5.5 A
Motor power kW	0.75 kW at 240 V AC 50/60 Hz 2.2 kW at 415 V AC 50/60 Hz 1.1 kW at 220/230 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Local signalling	Operating: LED (yellow)
Cable entry number	2 ISO20 top 2 ISO25 top 2 Pg 13 top 2 Pg 21 top 2 ISO20 bottom 2 ISO25 bottom 2 Pg 13 bottom 2 Pg 21 bottom 2 Pg 16 top 2 Pg 16 bottom

Width	78 mm
Height	160 mm
Depth	108 mm
Net weight	0.6 kg

Environment

Material	ABS (acrylonitrile butadiene-styrene)
IP degree of protection	IP65 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------