

Han F+B cover-HTE blue



| Part number | 09 15 513 5411 |
|--------------------|-------------------------------------|
| Specification | Han F+B cover-HTE blue |
| HARTING eCatalogue | https://b2b.harting.com/09155135411 |

Image is for illustration purposes only. Please refer to product description.

Identification

| Category | Hoods/Housings |
|-----------------------------|----------------------|
| Series | Han [®] F+B |
| Type of hood/housing | Protection cover |
| Description of hood/housing | for hoods |

Version

| Locking type | Screw locking |
|----------------------|--|
| Field of application | Connector for food+beverage industry |
| | Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts. |
| Details | Strain relief:A suitable strain relief is required to enable the F+B connectorto resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable. |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|---|
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP67 in locked position IP6K9K acc. to ISO 20653 |

Material properties

| Material (hood/housing) | Polypropylen |
|--------------------------|--------------|
| Roughness of the surface | ≤1.12 µm |
| Colour (hood/housing) | Blue |

Page 1 / 2 | Creation date 2020-03-26 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

| Material (seal) | Silicone |
|-----------------------------|-----------|
| Colour (seal) | Blue |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |
| EG1935/2004 | compliant |

Specifications and approvals

| | Ecolab Topactive 200 |
|-----------|-----------------------|
| | Ecolab Topactive 500 |
| | Ecolab Topax 66 |
| Approvals | Ecolab Topactive OKTO |
| | Ecolab Topax 990 |
| | FDA 21 CFR 177.1520 |
| | FDA 21 CFR 177.2600 |

Commercial data

| Packaging size | 1 |
|--------------------------------|--|
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440208 Cap for industrial connectors |