

Han F+B-HBM blue



Part number	09 15 513 0301
Specification	Han F+B-HBM blue
HARTING eCatalogue	https://b2b.harting.com/09155130301

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series	Han [®] F+B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight With three through holes for fixing screws

Version

Locking type	Screw locking
Field of application	Connector for food+beverage industry
	Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts.
Details	Strain relief:A suitable strain relief is required to enable the F+B connectorto resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.

Technical characteristics

Limiting temperature	-40 +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 in locked position IP6K9K acc. to ISO 20653

Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤1.12 µm



Material properties

Colour (hood/housing)	Blue
Material (seal)	EPDM Silicone
Colour (seal)	Blue
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
EG1935/2004	compliant

Specifications and approvals

•	• •	
	Ecolab Topactive 200	
		Ecolab Topactive 500
		Ecolab Topax 66
Approvals	Ecolab Topactive OKTO	
	Ecolab Topax 990	
		FDA 21 CFR 177.1520
		FDA 21 CFR 177.2600
CE		Yes
CE		165

Commercial data

Packaging size	1
Net weight	14 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors