

2.54mm Box Header

Double Row, Vertical, Through Hole Type

multicomp PRO

**RoHS
Compliant**




Specifications

Current Rating	: 3A AC/DC
Voltage Rating	: 250V AC/DC
Contact Resistance	: 20mΩ Max.
Insulation Resistance	: 1000MΩ Min.
Withstanding Voltage	: 600V AC for one minute
Operating Temperature Range	: -40°C to +105°C


Materials and Finish

Insulator	: PBT (UL94V-0)
Standard Colour	: Black
Contact	: Copper Alloy
Finish	: Gold Plated

Diagram



PCB Layout



Dimensions : Millimetres

Part Number Table

Description	Dimensions			Part Number
	A	B	C	
Header, Vertical, 2.54mm, 6POS, 2Row, TH, 1Key	15.28mm	5.08mm	12.96mm	MC-254-06-00-ST-DIP
Header, Vertical, 2.54mm, 8POS, 2Row, TH, 1Key	17.82mm	7.62mm	15.5mm	MC-254-08-00-ST-DIP
Header, Vertical, 2.54mm, 10POS, 2Row, TH, 1Key	20.36mm	10.16mm	18.04mm	MC-254-10-00-ST-DIP
Header, Vertical, 2.54mm, 12POS, 2Row, TH, 1Key	22.9mm	12.7mm	20.58mm	MC-254-12-00-ST-DIP
Header, Vertical, 2.54mm, 14POS, 2Row, TH, 1Key	25.44mm	15.24mm	23.12mm	MC-254-14-00-ST-DIP
Header, Vertical, 2.54mm, 16POS, 2Row, TH, 1Key	27.98mm	17.78mm	25.66mm	MC-254-16-00-ST-DIP
Header, Vertical, 2.54mm, 20POS, 2Row, TH, 1Key	33.06mm	22.86mm	30.74mm	MC-254-20-00-ST-DIP
Header, Vertical, 2.54mm, 24POS, 2Row, TH, 1Key	38.14mm	27.94mm	35.82mm	MC-254-24-00-ST-DIP
Header, Vertical, 2.54mm, 26POS, 2Row, TH, 1Key	40.68mm	30.48mm	38.36mm	MC-254-26-00-ST-DIP
Header, Vertical, 2.54mm, 30POS, 2Row, TH, 1Key	45.76mm	35.56mm	43.44mm	MC-254-30-00-ST-DIP

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

2.54mm Box Header

Double Row, Vertical, Through Hole Type

multicomp PRO

Description	Dimensions			Part Number
	A	B	C	
Header, Vertical, 2.54mm, 34POS, 2Row, TH, 1Key	50.84mm	40.64mm	48.52mm	MC-254-34-00-ST-DIP
Header, Vertical, 2.54mm, 40POS, 2Row, TH, 1Key	58.46mm	48.26mm	56.14mm	MC-254-40-00-ST-DIP
Header, Vertical, 2.54mm, 50POS, 2Row, TH, 1Key	71.16mm	60.96mm	68.84mm	MC-254-50-00-ST-DIP
Header, Vertical, 2.54mm, 60POS, 2Row, TH, 3Key	83.86mm	73.66mm	81.54mm	MC-254-60-00-ST-DIP
Header, Vertical, 2.54mm, 64POS, 2Row, TH, 3Key	88.94mm	78.74mm	86.62mm	MC-254-64-00-ST-DIP

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO