

PRODUCT-DETAILS

CEPY1-1001

ENCLOSURE CEPY1-1001



General Information

Extended Product Type	CEPY1-1001
Product ID	1SFA619821R1001
EAN	7320500358108
Catalog Description	ENCLOSURE CEPY1-1001
Long Description	Assembled Enclosure - 40mm Mushroom Emergency Stop - Twist Release - 2NC - Horizontally mounted

Ordering

E-Number (Norway)	4373373
E-Number (Sweden)	3711610
EAN	7320500358108
Minimum Order Quantity	1 piece
Customs Tariff Number	85369001

Dimensions

Product Net Width	0.065 m
Product Net Height	0.065 m
Product Net Depth / Length	0.079 m
Product Net Weight	0.138 kg

Container Information

Package Level 1 Width	0.1 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.1 m
Package Level 1 Gross Weight	0.105 kg

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Additional Information

Accessory Type	Enclosure
Color	Yellow/Light grey
Degree of Protection	Housing IP69K
Housing Material	Plastic
Material	Plastic
Number of Auxiliary Contacts NC	2
Product Main Type	CEPY1
Product Name	Enclosure
Product Range	Compact range
Product Type	CEPY
RoHS Date	0626 5

Certificates and Declarations (Document Number)

cURus Certificate	UL_E496500-20171020
Data Sheet, Technical Information	1SFC151007C0201
Declaration of Conformity - CE	2CMT2019-005802
Environmental Information	1SFC151009D0201
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2019-005802

Classifications

ETIM 4	EC002024 - Accessories for control circuit devices
ETIM 5	EC000200 - Enclosure for control circuit devices
ETIM 6	EC000225 - Control circuit devices combination in enclosure
ETIM 7	EC000225 - Control circuit devices combination in enclosure
Object Classification Code	S
UNSPSC	39121500
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Compact Range

