

PRODUCT-DETAILS

E219-D48

E219-D48 Indicator Light



General Information

Extended Product Type	E219-D48
Product ID	2CCA703422R0001
EAN	7612270939251
Catalog Description	E219-D48 Indicator Light
Long Description	Indicator light with maintenance-free LED, LED colour: green 115-250 VACPDC, 12-48 VACDCPDC, 110-220 VDCPDC Module width 0,5

Ordering

E-Number (Switzerland)	472352638
EAN	7612270939251
Minimum Order Quantity	10 piece
Customs Tariff Number	85365000

Dimensions

Product Net Width	9 mm
Product Net Height	85 mm
Product Net Length	93 mm
Product Net Depth / Length	58 mm
Product Net Weight	43 g

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	96 mm
Package Level 1 Height	76 mm
Package Level 1 Depth / Length	95 mm
Package Level 1 Gross Weight	40 g
Package Level 1 EAN	7612270939251

Environmental

RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
-------------	---

Additional Information

Color	Green
Degree of Protection	IP20
Number of LEDs	1
Power Loss	0.44 W
Product Main Type	E219
Product Name	Indicator Light
Rated Voltage (U _r)	48 V
Rated Operational Voltage	12 ... 48 V
RoHS Date	20170426
Standards	EN 62094-1
Voltage Range	12 ... 48 V AC/DC

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CCC441003C0101
Declaration of Conformity - CE	2CCC441003D0601
Environmental Information	2CCC441002C0201
Instructions and Manuals	2CCC441001C0201
RoHS Information	2CCC413008D0206

Classifications

ETIM 4	EC001657 - Indicator light for distribution board
ETIM 5	EC001657 - Indicator light for distribution board
ETIM 6	EC001657 - Indicator light for distribution board
ETIM 7	EC001657 - Indicator light for distribution board
Object Classification Code	P
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Command and Signalling devices → Control Switches, Pushbuttons and Indicator Lights

