

PRODUCT-DETAILS

PS2/58

PS2/58 - Busbar



General Information

Extended Product Type	PS2/58
Product ID	2CDL220001R1058
EAN	4016779556552
Catalog Description	PS2/58 - Busbar
Long Description	PS 2/58 Busbar

Ordering

E-Number (Sweden)	2102529
EAN	4016779556552
Minimum Order Quantity	1 piece
Customs Tariff Number	85369010

Dimensions

Product Net Width	14.8 mm
Product Net Height	29 mm
Product Net Length	1020 mm
Product Net Depth / Length	1020 mm
Product Net Weight	0.36 kg

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	80 mm
Package Level 1 Height	80 mm
Package Level 1 Depth / Length	1020 mm
Package Level 1 Gross Weight	3.81 kg

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Additional Information

Accessory Type	Busbar
Color	Grey
Housing Material	Light grey, RAL 7035
Mounting Position	Any
Number of Phases	2
Overvoltage Category	III
Pollution Degree	2
Product Main Type	Busbars PS
Product Name	Busbar
Rated Cross-Section	10 mm ²
Rated Frequency (f)	50 Hz 60 Hz DC
RoHS Date	20170228
Suitable For	S200 F200 DDA200
Suitable for Product Class	Miniature Circuit Breakers Residual Current Circuit Breakers Residual Current Circuit Breakers with Overcurrent Protection

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A8017
Declaration of Conformity - CE	2CDK446006D0403
Environmental Information	2CDU400029D0201
Instructions and Manuals	2CSC400002D0208
RoHS Information	2CDK440009K0203

Classifications

ETIM 4	EC000215 - Phase busbar
ETIM 5	EC000215 - Phase busbar
ETIM 6	EC000215 - Phase busbar
ETIM 7	EC000215 - Phase busbar
Object Classification Code	W
UNSPSC	39121614

WEEE Category

4. Large Equipment (Any External Dimension More Than 50 cm)

eClass

7.0 27371306

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs Accessories → Busbars and Accessories (IEC Range)

