

PRODUCT-DETAILS

## 316RAM6B

Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 16A, IP44 splashproof, minimized flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red



### General Information

Extended Product Name	316RAM6B
Product ID	2CMA100544R1000
EAN	7392696005449
Catalog Description	Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 16A, IP44 splashproof, minimized flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red
Long Description	Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 16A, IP44 splashproof, minimized flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red Clock Position Of Grounding Contact 6 hour Color code Red

### Ordering

E-Number (Sweden)	E2417583
E-Number (Finland)	2409599
E-Number (Norway)	1540749
EAN	7392696005449
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

### Dimensions

Product Net Width	73 mm
-------------------	-------

Product Net Height	89 mm
Product Net Length	99 mm
Product Net Depth / Length	99 mm
Product Net Weight	0.24 kg

### Container Information

Package Level 1 Width	154 mm
Package Level 1 Depth / Length	182 mm
Package Level 1 Height	378 mm
Package Level 1 Gross Weight	2.4 kg
Package Level 1 EAN	7392696007733
Package Level 1 Units	box 10 piece
Package Level 2 Units	450 piece

### Technical UL/CSA

Ampere Rating UL/CSA	16 A
Tightening Torque UL/CSA	7.1 in-lb

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1614201
REACH Declaration	2CMC700005D0001

### Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm <sup>2</sup>
Cable Diameter	13 ... 17 mm
Color	Red
Connection Type	Screw
Cover Color	Black
Degree of Protection	IP44
Frequency (f)	50 Hz 60 Hz
Function	Outlet
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#316RAM6B

Material	Plastic
Mounting Holes	66x66
Mounting Type	Angled
Number of Poles	4
Order Multiple	10 piece
Product Main Type	ERAM
Product Name	Panel mounted socket
Protection Type	Splashproof
Rated Current ( $I_n$ )	16 A
Rated Frequency (f)	50...60 Hz
Rated Voltage ( $U_r$ )	380 ... 415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 9005 - Jet Black

---

## Classifications

eClass	27440504
UNSPSC	39120000

---

## Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

---

## Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Socket Outlets for Panel Mounting

