

PRODUCT-DETAILS

232RAM6B

Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 32A, IP44 splashproof, minimized flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue



General Information

Extended Product type	232RAM6B
Product ID	2CMA100546R1000
EAN	7392696005463
Catalog Description	Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 32A, IP44 splashproof, minimized flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue
Long Description	Black Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 32A, IP44 splashproof, minimized flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue Clock Position Of Grounding Contact 6 hour Color code Blue

Ordering

E-Number (Sweden)	E2417585
E-Number (Finland)	2420004
E-Number (Norway)	1540751
EAN	7392696005463
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	94 mm
-------------------	-------

Product Net Height	99 mm
Product Net Length	104 mm
Product Net Depth / Length	104 mm
Product Net Weight	0.27 kg

Container Information

Package Level 1 Width	188 mm
Package Level 1 Depth / Length	175 mm
Package Level 1 Height	428 mm
Package Level 1 Gross Weight	2.7 kg
Package Level 1 EAN	7392696007757
Package Level 1 Units	box 10 piece
Package Level 2 Units	320 piece

Technical UL/CSA

Ampere Rating UL/CSA	32 A
Tightening Torque UL/CSA	10.6 in·lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1614201
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm ²
Cable Diameter	13 ... 21.5 mm
Color	Blue
Connection Type	Screw
Cover Color	Black
Degree of Protection	IP44
Frequency (f)	50 Hz 60 Hz
Function	Outlet
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#232RAM6B

Material	Plastic
Mounting Holes	75x75
Mounting Type	Angled
Number of Poles	3
Order Multiple	10 piece
Product Main Type	ERAM
Product Name	Panel mounted socket
Protection Type	Splashproof
Rated Current (I_n)	32 A
Rated Frequency (f)	50...60 Hz
Rated Voltage (U_r)	200 ... 250 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 9005 - Jet Black

Classifications

eClass	27440504
UNSPSC	39120000

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Socket Outlets for Panel Mounting

