

PRODUCT-DETAILS

4125P6W

Ind. P&S#4125P6W



General Information

Extended Product Type	4125P6W
Product ID	2CMA166828R1000
EAN	7392696668286
Catalog Description	Ind. P&S#4125P6W
Long Description	Plug, earthing sleeve position 6h, rated current 125A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416311
E-Number (Finland)	2421629
E-Number (Norway)	1563923
EAN	7392696668286
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	127 mm
Product Net Height	127 mm

Product Net Length	312 mm
Product Net Depth / Length	312 mm
Product Net Weight	1.54 kg
Mechanical Drawings	9AKK107492A4190

Container Information

Package Level 1 Width	138 mm
Package Level 1 Depth / Length	158 mm
Package Level 1 Height	345 mm
Package Level 1 Gross Weight	1.64 kg
Package Level 1 EAN	7392696668286
Package Level 1 Units	box 1 piece
Package Level 2 Units	66 piece

Technical UL/CSA

Ampere Rating UL/CSA	125 A
Tightening Torque UL/CSA	50 in·lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1025779
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	16 ... 50 mm²
Cable Diameter	24 ... 48 mm
Cable Entry Position	Cable entry, compression gland, internal and external cable clamp
Color	Red
Connection Type	Screw
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Plug

Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#4125P6W
Material	Plastic
Number of Poles	5
Order Multiple	1 piece
Product Main Type	TP
Product Name	Industrial Plug
Protection Type	Watertight
Rated Current (I_n)	125 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Plugs
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000040M0001
Installation Manual	2CMC000040M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440509
UNSPSC	39120000

Technical

Wire Size	3 ... 1 AWG
Tightening Torque	5.6 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Plugs

