

PRODUCT-DETAILS

432RPR6

Socket-outlet with RCD, 6h, 30mA, 32A, IP44,
3P+N+E



General Information

Extended Product Type	432RPR6
Product ID	2CMA168300R1000
EAN	7392696683005
Catalog Description	Socket-outlet with RCD, 6h, 30mA, 32A, IP44, 3P+N+E
Long Description	Socket-outlet with RCD, earthing sleeve position 6h, 30mA, rated current 32A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2466307
E-Number (Finland)	2421482
E-Number (Norway)	2466307
EAN	7392696683005
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	120 mm
Product Net Height	149 mm

Product Net Length	243 mm
Product Net Depth / Length	243 mm
Product Net Weight	1.2 kg

Container Information

Package Level 1 Width	152 mm
Package Level 1 Depth / Length	120 mm
Package Level 1 Height	265 mm
Package Level 1 Gross Weight	1.3 kg
Package Level 1 EAN	7392696683005
Package Level 1 Units	box 1 piece
Package Level 2 Units	125 piece

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1507476
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm²
Cable Diameter	13 ... 21.5 mm
Cable Entry Position	Top
Cable Outlets Per Side	2xØ25
Color	Red
Connection Type	Screw
Degree of Protection	IP44
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Surface socket outlet with RCD, 30 mA
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#432RPR6
Material	Plastic
Mounting Holes	171x90
Mounting Type	Vertical
Number of Poles	5

Number of RCDs 30mA	1
Number of RCDs	1
Order Multiple	1 piece
Product Main Type	CRPR
Product Name	Industrial Socket Outlet with Protection
Protection Type	RCD
Rated Current (I_n)	32 A
Rated Residual Current	30 mA
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Sub-Function	Cable entry, knock-outs 2xØ25mm
Suitable For	Socket Outlets with RCD
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000039M0001
Installation Manual	2CMC000039M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39121406

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Socket Outlets with RCD

