

PRODUCT-DETAILS

AT42R3

AT42R3 Dist. Board 3R w.door



General Information

Extended Product Type	AT42R3
Product ID	2CPX071682R9999
EAN	4011617716822
Catalog Description	AT42R3 Dist. Board 3R w.door

Long Description	compact distribution boards, series AT, partly assembled cabinet, for the internal use, with Door, class of protection II (double insulated), in combination with earthing set (accessory) we can achieve protection class 1, degree of protection IP43, applicable standards: EN 61439-1, EN 61439-3, Rated operational voltage 400V AC 50/60 Hz, rated current 125 A, powder-coated, in RAL 9016, enclosure out of sheet steel, metal door, door out of sheet steel, in RAL 9016, with Standard closure, door opening angle 130 degree, door hinge right or left, cable entry on top via membrane flange mounted, on bottom via flange opening pre-punched, dimensions in mm (H x W x D): 674 x 574 x 140, Ratchet unit 4 GU, panel width 2, 3-rows, Space units 72, Row distance in mm: 150, covers out of Plastic, 90 degree press and turn closure, RAL 7035, with N/PE Quick-terminal, cable fastening rail integrated, expanded with distributor fields, device support removable
------------------	--

Ordering

EAN	4011617716822
Minimum Order Quantity	1 piece
Customs Tariff Number	85381000
Replacement Product ID (NEW)	2CPX052235R9999

Dimensions

Product Net Width	574 mm
Product Net Height	674 mm
Product Net Depth / Length	140 mm
Product Net Weight	15.006 kg

Container Information

Package Level 1 Units	pack 1 piece
Package Level 1 Width	580.000 mm
Package Level 1 Height	675.000 mm
Package Level 1 Depth / Length	145.000 mm
Package Level 1 Gross Weight	15.184 kg
Package Level 1 EAN	4011617716822
Package Level 2 Units	pallet (lift) 20 piece
Package Level 2 Width	800.000 mm
Package Level 2 Height	1630.000 mm
Package Level 2 Depth / Length	1200.000 mm
Package Level 2 Gross Weight	312 kg

Additional Information

Color	Traffic white
Cover Plate Type	Door
Degree of Protection	IP43
Design	Wall cabinet top-mount
DIN Place Units	72
Enclosure Type	compact distribution boards
Field Width	2
Housing Material	Steel
Interior Depth	140 mm
Meter Boards	0
Mounting Position	Wall cabinet top-mount
Mounting Type	Wall cabinet top-mount
Number of Rows	3
Power Loss	$\Delta t = 20K$ 53.9 W $\Delta t = 25K$ 71.2 W $\Delta t = 30K$ 89.3 W
Product Main Type	AT
Product Name	AT42R3 Dist. Board 3R w.door
Protection Class	Isolated
Rated Current (I_n)	125 A

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CPC000001C0101
	2CPC000002C0101
	2CPC000031C0101
	2CPC000187C0101
	2CPC000188C0101
Declaration of Conformity - CE	No declaration needed
Environmental Information	2CPC100001X0201
Instructions and Manuals	2CPC100501M5601
	2CPC121464M5601
	2CPC130119M5601

Classifications

ETIM 4	EC000214 - Small distribution board
ETIM 5	EC000214 - Small distribution board
ETIM 6	EC000214 - Small distribution board
ETIM 7	EC000214 - Small distribution board
Object Classification Code	U
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosures → Sub Distribution Boards → Compact Distribution Boards - Modules Assembled

