

Protect It! 6-Outlet Surge Protector, 6-ft cord, 1340 Joules, Diagnostic LED

MODEL NUMBER: TLM606HJ



Highlights

- 6 outlets / 6 ft. cord
- 1340 joule rating

Package Includes

- TLM606HJ surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's TLM606HJ surge suppressor offers complete AC surge suppression for comprehensive protection of personal computers, home stereos, televisions, VCRs, DVD players, power tools and other electrical and electronic equipment. Heavy-duty AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM606HJ offers 6 total outlets, a 6 foot power cord and diagnostic LED to warn of suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing offers convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input - 6 ft. AC line cord with NEMA 5-15P plug/Output - 6 NEMA 5-15R outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Metal strip

SUPPRESSION: AC: 150V RMS Clamping/1340 joules/400V UL1449 3rd Edition

Features

- 6 outlets
- 6 ft. cord
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- Diagnostic LED confirms suppressor "protection present" (green)
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 1 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated on/off switch with integrated 15 amp circuit breaker



- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332135698
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of outlets
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Illuminated on/off switch with integrated 15 amp circuit breaker
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	



AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Anti-Microbial Protective Coating	No
Color	Light Gray
Color (AC Line Cord)	Light Gray
Form Factors Supported	Supports floor / wall / desktop placement
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Metal top enclosure, plastic bottom insert
Outlets Measurement (Center to Center)	38.89mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	3.81 x 10.92 x 36.32
Shipping Dimensions (hwd / in.)	1.50 x 4.30 x 14.30
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
Unit Dimensions (hwd / cm)	3.8 x 31.8 x 6.3
Unit Dimensions (hwd / in.)	1.5 x 12.5 x 2.5
Unit Weight (kg)	0.64
Unit Weight (lbs.)	1.4
SPECIAL FEATURES	
Rotatable Outlets	No
CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>