

# Farnell 1124394

**Manufacturer:** VOLEX **Manufacturer Part No:** X-428796A

non-rewireable lead for use in Australia, New Zealand, Fiji, Papua New Guinea and ROC. The plug complies with **AS3112-1990** and **NZSS198-1967**. Two and a half metres of 1.0mm<sup>2</sup> cable to harmonised code **H05VV-F** interconnect the moulded plug and 10A IEC free socket. The socket is approved to **NEMKO, NF-USE, DEMKO, CEBEC, BSI, IMQ, VDE, SEV, KEMA-KEUR, FI, OVE,** and **SEMKO**

Current rating 10 Plug contacts Brass  
Cable and Connector housings Black Socket Contacts Phosphor Bronze

## Description

- LEAD, AUSTRALIAN BLACK 2.5M
- Connector type A:10A Australian Plug
- Connector type B:IEC Socket
- Length, lead:2.5m
- Cable type:SVT3X18
- Voltage rating, AC:250V
- Colour:Black
- Approval Bodies:BSI, VDE, NF-USE, OVE, CEBEG, NEMKO, DEMKO, SEMKO, IMQ, SEV, KEMA-KEUR
- Approval category:AUS AS3112-1990/NZ NZSS198-1967
- Area, conductor CSA:1mm<sup>2</sup>
- Current rating:10A
- Diameter, cable max:7.2mm
- Diameter, cable min:6.9mm
- Material:PVC
- Material, contact:Phosphor Bronze
- Material, contact connector A:Brass
- Material, plug body:PVC