

## Shielded Cat5e FTP Patch Cables Cat.5e STP Patch Cables

Part No: 1962 - (Length) + (Colour) see chart

The STP cables are manufactured using stranded core, foil screened Cat.5e cable and a shielded plug fitted with matching strain relief boot. All cables are available from stock in the lengths listed below. Custom made cables are available upon request. For full details of this service please contact our sales department.

### Features & Benefits

- Manufactured using quality components
- Connectors: 50 micron gold, shielded RJ45 plugs
- Cable: EIA/TIA T568-A, Cat.5e stranded, foil shielded UL approved cable
- Wired to 258A specification using a quality shielded plug and strain relief boot
- Suitable for all current data, voice and ISDN patching
- Choice of 6 colours for easy recognition





# Shielded Cat5e FTP Patch Cables

## Cat.5e STP Patch Cables

Part No: 1962 - (Length) + (Colour) see chart

### Part Number Chart

Length	Beige 	Black 	Blue 	Green 	Red 	Yellow 
0.3 Metre	1962-0.3	-	-	-	-	-
0.5 Metre	1962-0.5	1962-0.5BK	1962-0.5B	1962-0.5G	1962-0.5R	1962-0.5Y
1 Metre	1962-1	1962-1BK	1962-1B	1962-1G	1962-1R	1962-1Y
1.5 Metre	1962-1.5	-	1962-1.5B	-	-	-
2 Metre	1962-2	1962-2BK	1962-2B	1962-2G	1962-2R	1962-2Y
3 Metre	1962-3	1962-3BK	1962-3B	1962-3G	1962-3R	1962-3Y
5 Metre	1962-5	1962-5BK	1962-5B	1962-5G	1962-5R	1962-5Y
8 Metre	1962-8	-	-	-	-	-
10 Metre	1962-10	1962-10BK	1962-10B	1962-10G	1962-10R	1962-10Y
15 Metre	1962-15	-	-	-	-	-
20 Metre	1962-20	-	-	-	-	-
25 Metre	1962-25	-	-	-	-	-
30 Metre	1962-30	-	-	-	-	-
50 Metre	1962-50	-	-	-	-	-
100 Metre	1962-100	-	-	-	-	-