

EXPANDED CHARGING INFORMATION

- Enhanced sensory experience through the progression of multiple colors linked with audio notifications



MAXIMIZED PERFORMANCE

- Helps maximize battery performance by ensuring a full charge, while not overcharging or damaging your batteries



PLEASING, EASY TO USE DESIGN

- Compact and sleek for pleasing appearance and easy storage
- Detailed elements increase ease of use



Pro Charger



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer® NiMH batteries.

[Download Instructions \(Americas\)](#)
[Download Instructions \(Rest of World\)](#)

Product Detail:

Designation: Pro Charger

Model: CHPRO

Color: Black

Charge Capability: "AA" (2) or (4)
 "AAA" (2) or (4)

Note: When charging only 2 batteries, place batteries in the two positions to the left or right.

Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)
	AA	1300-2000	3-4 hrs
AA	2000-2300	4-5 hrs	
AAA	500-800	3-4 hrs	

Shutoff Mechanism: Delta V Detection

Timer Control: 5 hrs

Charging Current: "AA" 500mA
 "AAA" 220mA

Trickle Charge: None

Input Rating: 100-240VAC, 50-60Hz, 7W

Charging Indication: Sound Indicators - Single Beep/Start - Double/Done
 3 Stage Status Indicators: Red - Charging (0-49%)
 Amber - Charging (50-99%), Green - Fully Charged

Typical Weight: 113 grams

Dimensions (mm): 116 x 70 x 50 (H x L x W)

Safety Features: Short Circuit and Reverse Polarity Protection
 Primary Battery Detection
 Bad Battery Detection
 Delta V Charging Cut Off
 Safety Timer to Prevent Overcharge

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

Contents herein do not constitute a warranty.