

Pneumatic muffler U-1/8-B

Part number: 6841

FESTO



Data sheet

Feature	Value
Type code	U
Mounting position	Any
Symbol	00991473
Operating pressure for entire temperature range	0 bar ... 10 bar
Flow rate with respect to atmosphere	1340 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Noise level	74 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	8 g
Pneumatic connection	G1/8
Cushioning insert material	PE
Material of screwed trunnion	Aluminum
Note on materials	RoHS-compliant Free of copper and PTFE
Housing material	Aluminum