


Flow control/muffler GRU-1/4-B

Part number: 9517

FESTO



Data sheet

| Feature | Value |
|---|---|
| Type code | GRU |
| Valve function | Sound pressure flow control function |
| Selection of additional function | With pneumatic muffler |
| Pneumatic connection 1 | G1/4 |
| Adjusting element | Slotted screw |
| Type of mounting | Screw-in |
| Standard flow rate 6->0 bar | 0 l/min ... 1500 l/min |
| Ambient temperature | -10 °C ... 70 °C |
| Housing material | Aluminum |
| Mounting position | Any |
| Symbol | 00991451 |
| Operating pressure for entire temperature range | 0 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Temperature of medium | -10 °C ... 70 °C |
| Product weight | 25 g |
| Cushioning insert material | PE |
| Material of screwed trunnion | Die-cast aluminum |
| Note on materials | RoHS-compliant |
| Material of adjusting screw | PA |