## Exhaust air flow control valve GRE-1/2 Part number: 10353







## **Data sheet**

Feature	Value
Type code	GRE
Valve function	Sound pressure flow control function
Selection of additional function	With pneumatic muffler
Pneumatic connection 1	G1/2
Adjusting element	Slotted screw
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	3600 l/min
Standard flow rate 6->0 bar	0 l/min 3600 l/min
Operating pressure	0 bar 10 bar
Ambient temperature	-10 °C 70 °C
Mounting position	Any
Symbol	00991451
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C 70 °C
Product weight	75 g
Material of screwed trunnion	Wrought aluminum alloy
Note on materials	RoHS-compliant
Seals material	NBR
Material of adjusting screw	Brass