## Pneumatic muffler AMTE-M-LH-G38 Part number: 1205862



**FESTO** 

## **Data sheet**

Feature	Value	
Type code	AMTE	
Mounting position	Any	
Pack size	10	
Symbol	00991473	
Operating pressure	0 bar 10 bar	
Flow rate with respect to atmosphere	5430 l/min	
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]	
Information on operating and pilot media	Operation with oil lubrication possible	
Corrosion resistance class (CRC)	1 - Low corrosion stress	
Noise level	82 dB(A)	
Ambient temperature	-40 °C 80 °C	
Product weight	26 g	
Pneumatic connection	G3/8	
Cushioning insert material	Bronze	
Material of screwed trunnion	Brass	
Note on materials	RoHS-compliant	