



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O

Complementary

[Ie] rated operational current	35 A AC-3
Motor power kW	15 kW at 380/400 V AC 50/60 Hz 15 kW at 415 V AC 50/60 Hz 15 kW at 440 V AC 50/60 Hz 7.5 kW at 220/230 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz 18.5 kW at 660/690 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	35 A
[Uc] control circuit voltage	380 V AC 50/60 Hz
Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom
Width	101 mm
Height	201 mm
Depth	153.5 mm

Net weight	4.32 kg
------------	---------

Environment

Material	Polycarbonate
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------