



## Main

|                                    |                                                                                                                |
|------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Range                              | TeSys                                                                                                          |
| Device short name                  | GS2AP                                                                                                          |
| Product or component type          | Terminal shroud                                                                                                |
| Accessory / separate part category | Protection accessory                                                                                           |
| Range compatibility                | TeSys GS GS2S<br>TeSys GS GS2T<br>FuPact GS GSB630<br>FuPact GS GSB800<br>FuPact GS GSD630<br>FuPact GS GSD800 |
| Standards                          | IEC<br>UL<br>CSA                                                                                               |
| Poles description                  | 3P                                                                                                             |
| Switch rated current               | 600 A<br>630 A<br>800 A                                                                                        |

## Complementary

|            |         |
|------------|---------|
| Net weight | 0.50 kg |
|------------|---------|

## Offer Sustainability

|                            |                                                  |
|----------------------------|--------------------------------------------------|
| Sustainable offer status   | Green Premium product                            |
| REACH free of SVHC         | Yes                                              |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                              |
| Mercury free               | Yes                                              |
| RoHS exemption information | <a href="#">Yes</a>                              |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>           |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|