



Main

Range	TeSys
Device short name	LB1LD
Product or component type	Protection module
Range compatibility	TeSys Integral contactor breaker
Poles description	3P
Utilisation category	AC-1
[Ue] rated operational voltage	690 V AC
Thermal protection adjustment range	35...50 A
Magnetic tripping current	150...300 A
Trip unit technology	Thermal-magnetic
Protection type	Phase imbalance
Thermal overload class	Class 20

Complementary

Net weight	0.78 kg
------------	---------

Environment

Standards	NF C 63-120
Protective treatment	TH
IP degree of protection	IP20 B

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------