



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1K
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contacteur ordered separately Circuit-breaker ordered separately Padlocking device
Product compatibility	LG7
Control type	Without

Complementary

Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Width	175 mm
Depth	142 mm
Net weight	0.5 kg

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------