



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	4P LC1D40008...D80008 3P LC1D80...D95 4P LC1D80004

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	Bidirectional peak limiting diode
[Uc] control circuit voltage	24 V DC
Maximum peak voltage	2 Uc
Net weight	0.04 lb(US) (0.018 kg)

Environment

Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901931249
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------