
## Pressure regulator MS4-LR-1/4-D6-AS Part number: 529417

**FESTO** 





## **Data sheet**

| Feature                                  | Value  |
|--|--|
| Size                                     | 4  |
| For use in the food industry             | See supplementary material information   |
| Type code                                | MS4-LR   |
| Series                                   | MS   |
| Actuator lock                            | Rotary knob with detent can be closed with accessories                             |
| Mounting position                        | Any  |
| Design                                   | Directly controlled diaphragm regulator  |
| Controller function                      | Outlet pressure constant<br>With return flow function<br>With secondary exhausting |
| Symbol                                   | 00991558   |
| Pressure gauge                           | with pressure gauge  |
| Operating pressure                       | 0.8 bar 14 bar   |
| Pressure regulation range                | 0.3 bar 7 bar  |
| Max. pressure hysteresis                 | 0.25 bar   |
| Standard nominal flow rate               | 1800 l/min   |
| Operating medium                         | Inert gas<br>Compressed air as per ISO 8573-1:2010 [7:4:4]                         |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                 |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress  |
| Storage temperature                      | -10 °C 60 °C   |
| Temperature of medium                    | -10 °C 60 °C   |
| Ambient temperature                      | -10 °C 60 °C   |
| Product weight                           | 225 g  |
| Type of mounting                         | Front panel mounting Optionally: Line installation With accessories                |
| Pneumatic connection 1                   | G1/4   |
| Pneumatic connection 2                   | G1/4   |
| Note on materials                        | RoHS-compliant   |
| Material of sub-base                     | Die-cast aluminum  |
| Material of operator panel               | POM<br>PA  |
| Seals material                           | NBR  |

| Feature                        | Value             |
|--------------------------------|-------------------|
| Compressed air filter material | PE                |
| Housing material               | Die-cast aluminum |
| Diaphragm material             | NBR               |