
Pressure regulator MS4-LR-1/4-D7-AS Part number: 529419

FESTO





Data sheet

Feature	Value
Size	4
For use in the food industry	See supplementary material information
Type code	MS4-LR
Series	MS
Actuator lock	Rotary knob with detent can be closed with accessories
Mounting position	Any
Design	Directly controlled diaphragm regulator
Controller function	Outlet pressure constant With return flow function With secondary exhausting
Symbol	00991558
Pressure gauge	with pressure gauge
Operating pressure	0.8 bar 14 bar
Pressure regulation range	0.5 bar 12 bar
Max. pressure hysteresis	0.25 bar
Standard nominal flow rate	1700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-10 °C 60 °C
Temperature of medium	-10 °C 60 °C
Ambient temperature	-10 °C 60 °C
Product weight	225 g
Type of mounting	Front panel mounting Line installation Optionally: With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Material of operator panel	PA POM
Seals material	NBR

Feature	Value
Compressed air filter material	PE
Housing material	Die-cast aluminum
Diaphragm material	NBR