

Flat Cables

33MIL (0.847mm), Hitachi Cable (150V, 105°C)

Specifications

Insulation Resistance: 5MΩ / km min. at 20°C
Withstanding Voltage: 1,500V AC / min.
Voltage Rating: 150V max.
Conductor Resistance: 362Ω / km max. at 20°C
Operating Temp. Range: -20°C to +105°C

Materials and Finish

Insulation: PVC
Conductor: 30 AWG (7/0.1mm) stranded Cu-wire



Features

- 33MIL, 0.847mm pitch flat cable designed for termination with DIN41612 IDC connectors (96 pos.)
- UL Style No. 2678

Part Number (Details)

TFC30 - 96 (0.847) *

Series No.

No. of Conductors:
96

Packing Sizes:
- = In Rolls (61 meters)
/ M = 1 meter

Standard Cable Length

see Part Number (Details)

Cable Dimensions

