



General ordering data

Order No.	1277700000
Part designation	Klippon POK 6
Version	Housings, 90 mm, 160 mm, 260 mm, glass fibre-reinforced polyester
EAN	4032248414857
Qty	1

Dimensions

Fixing dimension, width	240 mm
Fixing dimension, height	110 mm
Height	90 mm
Length	160 mm
Width	260 mm

General details

Enclosure fixing	Holes 6 mm
Sealing material	Polyurethane und chloroprene
Cover fixing	4 stainless steel M6 screws
Version cover	closed
Class of protection to EN 60529	IP 66
Weight	1710 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

Screwed cable glands top/bottom

M 25	5
M 12	30
M 40	3
M 16	24
M 32	4
M 20	14
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M20	4
M25	2
M32	2
M12	11
M40	1
M16	6
Side of enclosure	left / right

Classifications

ETIM 2.0	EC000058
ETIM 3.0	EC000058
eClass 4.1	27-14-12-06
eClass 5.0	27-14-91-07
eClass 5.1	27-14-91-07

Related products

Height	Length	Width
90 mm	160 mm	260 mm