



Main

Range	TeSys
Device short name	LA9D
Product or component type	Suppressor module
Product compatibility	Motor starter
Range compatibility	TeSys Integral contactor breaker

Complementary

Mounting mode	Clip-on
Suppressor technology	RC circuit
[Uc] control circuit voltage	<= 250 V AC 50/60 Hz
Maximum peak voltage	3 Uc 400 Hz
Net weight	0.01 kg

Environment

Standards	VDE 0106 IEC 60337-1
Protective treatment	TH
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------