



## Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	3P LC1D80...D150

## Complementary

Mounting mode	By screws
Suppressor technology	RC circuit
[Uc] control circuit voltage	50...127 V AC 50/60 Hz
Maximum peak voltage	3 Uc

## Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

### Contractual warranty

Warranty	18 months
----------	-----------