

PRODUCT-DETAILS

FLH0410

LT-H FLEXIBLE CONDUIT 20MM 10M



General Information

Extended Product Type	FLH0410
Product ID	7TCA297020R0141
EAN	5011949202948
Catalog Description	LT-H FLEXIBLE CONDUIT 20MM 10M
Long Description	Liquid Tight, High Temperature Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 10 Meters, Galvanised Steel Core, String Packing with Thermoplastic Rubber Covering, Black

Ordering

EAN	5011949202948
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	8.46 lb 3.837 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Extreme Temperature Environments
Brand / Label	Kopex
Color	Black
Flexibility	High
Inside Diameter	15.9 mm
Material	Galvanized Steel Core with String Packing and Thermoplastic Rubber Coating
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.1 mm
Product Name	flex metal conduit
Product Type	Liquid Tight High Temperature Conduit
Radius	80 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210276618

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLH0410
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLH0410

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

