

PRODUCT-DETAILS

# KSU0530

## KS FLEX CONDUIT 25MM S/S316 30M



### General Information

Extended Product Type	KSU0530
Product ID	7TCA297070R0085
EAN	5011949221758
Catalog Description	KS FLEX CONDUIT 25MM S/S316 30M
Long Description	Very Flexible, Metallic Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 24.7mm, Inside Diameter 21.1mm, Static Bend Radius 45mm, Reel Length 30 Meters, IP40 Rating, Uncovered Stainless Steel AISI 316L, Metallic

### Ordering

EAN	5011949221758
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	15.36 lb 6.966 kg
--------------------	----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

## Additional Information

Application	Indoors - Light Industrial, Buildings Marine, Corrosive Environments
Brand / Label	Kopex
Color	Metallic
Flexibility	High
Inside Diameter	21.1 mm
Material	316 Stainless Steel
Nominal Size	3/4 in
Number of Batteries	0
Outside Diameter	24.7 mm
Product Name	flexible metal conduit
Product Type	Flexible, Metallic Conduit
Radius	Static: 45 mm
Special Functions	Contains No Flame Propagating Materials
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210277745

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	KSU0530
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	KSU0530

## Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5539 >> Flexible Metallic Conduit

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

