

PRODUCT-DETAILS

# EXQM0606

## EXE LT STR 32MM FTNG N/P BR M32



Product image  
not available

### General Information

Extended Product Type	EXQM0606
Product ID	7TCA297120R0195
EAN	5011949001305
Catalog Description	EXE LT STR 32MM FTNG N/P BR M32
Long Description	Connector for Liquid Tight Conduit, Straight, Conduit Size 1 Inch/32mm, Thread Size M32, For Use in Industrial and Zone 2 Applications, IP66-67 Rating, Nickel Plated Brass

### Ordering

EAN	5011949001305
Customs Tariff Number	7412200035

### Dimensions

Product Net Weight	.31 lb 140.59 g
--------------------	--------------------

### Container Information

Package Level 1 Units	2 piece
Package Level 2 Units	10 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

### Additional Information

Application	For Use in Industrial and Zone 2 Applications to Connect Conduit Systems
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Straight Connector for Liquid Tight Conduit
Size	Conduit Size 32mm ; M32 Thread
Standards	BS EN 61386
Surface Finishing	Nickel Plated
Temperature Range	-50 to 130 °C
UPC	786210276113

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXQM0606
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXQM0606

### Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available