Note: This datasheet may be out of date. Please download the latest datasheet of LQG15HN22NH02# from the official website of Murata Manufacturing

LQG15HN22NH02#

"#" indicates a package specification code.

Size Code 1005 (0402) in mm (in inch), Multilayer Type
















< List of part numbers with package codes > LQG15HN22NH02J LQG15HN22NH02D LQG15HN22NH02B



Appearance & Shape













References

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	50000
D	180mm Paper Tape	10000
В	Bulk(Bag)	1000

Mass (typ.)	
1 piece	0.001g

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





${\sf Please \ download \ the \ latest \ data sheet \ of \ LQG15HN22NH02\# \ from \ the \ official \ website \ of \ Murata \ Manufacturing}}$

LQG15HN22NH02#

"#" indicates a package specification code.

Note: This datasheet may be out of date.



L size	1.0±0.05mm
W size	0.5±0.05mm
T size	0.5±0.05mm
Size code inch (mm)	0402 (1005)
Inductance	22nH±3%
Inductance Test Frequency	100MHz
Rated current (Itemp) (Based on Temperature rise)	350mA
Max. of DC resistance	0.58Ω
Q(min.)	8
Q Test Frequency	100MHz
Self resonance frequency (min.)	1800MHz
Operating Temperature Range(Self- temperature rise is not included)	-55°C to 125°C
Series	LQG15HN_02

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Please download the latest datasheet of LQG15HN22NH02# from the official website of Murata Manufacturing


LQG15HN22NH02#


"#" indicates a package specification code.

Note: This datasheet may be out of date




The charts below may show another part number which shares its characteristics.





LQG15HN22NH02 Q



LQG15HN22NH02 |Z|

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

