Note: This datasheet may be out of date. Please download the latest datasheet of LQW18ASR12G0Z# from the official website of Murata Manufacturing

LQW18ASR12G0Z#

"#" indicates a package specification code.

Designed under Industrial Global Standard


















< List of part numbers with package codes > LQW18ASR12G0ZB LQW18ASR12G0ZJ LQW18ASR12G0ZD



Appearance & Shape





(in mm)

References

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	500
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000

Mass (typ.)	
1 piece	0.003g

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date

Please download the latest datasheet of LQW18ASR12G0Z# from the official website of Murata Manufacturing

LQW18ASR12G0Z#

"#" indicates a package specification code.



L size	1.6±0.2mm
W size	0.8±0.3mm
T size	0.8±0.2mm
Size code inch (mm)	0603 (1608)
Inductance	120nH±2%
Inductance Test Frequency	150MHz
Rated current (Itemp) (Based on Temperature rise)	300mA
Max. of DC resistance	0.65Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Q(min.)	32
Q Test Frequency	150MHz
Self resonance frequency (min.)	1300MHz
Series	LQW18AS_0Z

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

