

# CyMotion Expert Combo

## G86-22000



### Facts & Features

- Extremely robust with a long life span
- Impervious to dirt and liquid
- Compact, ergonomic design
- 8 HotKeys, KeyM@n key and double programming of the F keys for control of multimedia and Internet functions
- Long-life accuracy of keyboard strokes
- 20 % larger keys
- PC- and MAC-compatible due to USB interface

### Delivery volume

- 1 CyMotion Expert keyboard
- 1 adapter USB-PS/2
- 1 printed manual

### Approvals

- FCC, cURus, GS, CE, c-tick, GOST-R
- Microsoft Windows™XP

### System requirements

- USB or PS/2 interface

### Technical data

- Number of buttons:  
104 + 9 = international layout with Windows™ and additional keys  
105 + 9 = european layout with Windows™ and additional keys
- Weight:  
approx. 880 g (keyboard)  
approx. 1200 g (with packaging)
- Dimensions:  
approx. 462 x 175 x 36 mm (keyboard)  
approx. 520 x 232 x 42 mm (packaging)
- Cable length:  
approx. 1.80 m
- Storage temperature:  
-20 °C to 60 °C
- Operating temperature:  
0 °C to 50 °C
- Operating life of individual keys:  
> 20 million operations
- Interface:  
USB (PS/2 via adapter)
- Current consumption:  
typ. 16 mA
- Packaging unit:  
11 keyboards per box  
12 boxes per pallet
- Guarantee period:  
2 years

## Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Country version</i>	<i>EAN-Code</i>
G86-22000BEADAB	black	114	Belgium	4025112052309
G86-22000BEAEAB	light grey	114	Belgium	4025112052200
G86-22000CHADAB	black	114	Switzerland	4025112052316
G86-22000CHAEAB	light grey	114	Switzerland	4025112052217
G86-22000DEADAB	black	114	Germany	4025112052323
G86-22000DEAEAB	light grey	114	Germany	4025112052224
G86-22000DKAEAB	light grey	114	Denmark	4025112057359
G86-22000ESADAB	black	114	Spain	4025112052330
G86-22000ESAEAB	light grey	114	Spain	4025112052231
G86-22000EUADAB	black	113	US-English with €	4025112052347
G86-22000FRADAB	black	114	France	4025112052354
G86-22000FRAEAB	light grey	114	France	4025112052255
G86-22000GBADAB	black	114	UK-English	4025112052361
G86-22000GBAEAB	light grey	114	UK-English	4025112052262
G86-22000ITADAB	black	114	Italy	4025112052378
G86-22000ITAEAB	light grey	114	Italy	4025112052279
G86-22000RGADAB	black	114	US-English / cyrillic	4025112052385
G86-22000RGAEAB	light grey	114	US-English / cyrillic	4025112052286
G86-22000SLADAB	black	114	Slovenia	4025112052392
G86-22000SLAEAB	light grey	114	Slovenia	4025112052293

Cherry Electrical Products Ltd  
Unit L, Airport Executive Park  
President Way, Luton, Beds  
LU2 9NY

Phone: +44 (0) 1582 506140  
Fax: +44 (0) 1582 506176  
Internet: [www.cherryuk.co.uk](http://www.cherryuk.co.uk)

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.  
Technical data relates to product specifications only.  
Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

