


- 230 V utgangsspenning fra 12 el. 24 V batteri
- Strøm til TV/Video, Husholdningsapparat, batteriadere (laptop, mobiltelefon), instrumenter, verktøy og annet utstyr
- Ideelt for profesjonelt og mobilt utstyr og for camping, hytte, båt og bil
- Innebygget alarm
- Kortslutningssikker
- Fjernkontroll som ekstrautstyr
- Tilgjengelig i 12 V og 24 V spenningsversjoner
- "E"-merket for kjøretøy direktivet (95/54/EC)
- 230 V output voltage from 12 or 24 V battery
- Power up TV/Video, appliances, battery chargers (laptop, mobile phones), instruments, tools and other equipment
- Ideal for industrial and mobile applications and for caravans, boats, and cars/trucks
- Built-in alarm
- Short circuit proof
- Remote control optional
- Available in 12 V and 24 V voltage versions
- "E"-marked vehicle directive ref. (95/54/EC)



Tekniske data	Technical specifications	12 V	24 V
Inngangsspenning	Input voltage	10-15 VDC	20-30 VDC
Utgangsspenning	Output voltage	230 VAC +5/-10% (50 Hz)	
Utgangseffekt	Output power	1000 W	
• Kontinuerlig:	• Continuous:	2000 W	
• Kortvarig:	• Intermittent:		
Tomgangsstrøm	No load current	< 1,8 A	< 1,0 A
Kurveform	Output wave form	Ren sinus/Pure sine wave	
Effektivitet	Efficiency	>90%	
Alarm ved lav batterispenning	Low battery alarm	10,7 V	21,4 V
Avbrudd ved lav batterispenning	Low battery shut-down	10 V	20 V
Elektrisk sikkerhetsstandard:	Electrical safety standard:	EN 60950	
EMC standarder	EMC standards		
• Emisjon:	• Emission:	EN 61000-6-3,95/54/EC	
• Immunitet:	• Immunity:	EN 61000-6-1,95/54/EC	
Sikring	Protection	Mot lav inngangsspenning, inngang mot overspenning, alarm ved lav batt.spenning, termisk sikret, overlast beskyttet og kortslutningssikker	
		Input low voltage, input over voltage, low battery alarm, over temperature, overload protection and short circuit proof	
MTBF	MTBF	55.000 Timer/Hours	
DC terminaler	DC terminals	Skruterminaler Terminal blocks (screw terminals)	
Mål (LxBxH)	Dimensions (LxWxH)	395 x 238 x 83mm	
Vekt	Weight	4 kg	

28122007

www.mascot.no
sales@mascot.no

Phone:
Fax:

Main Office
PO Box 177
N-1601 FREDRIKSTAD
NORWAY
+47 69 36 43 00
+47 69 36 43 01

Mascot UK
Box 2090, Salisbury
Wiltshire SP2 2BH
UK
+44 1722 504 853
+44 845 299 1210

Mascot DE-AT-CH-BENELUX
Hirschbergstr. 28/7
D-74838 LIMBACH
GERMANY
+49 6287 95140
+49 6287 95141

Tettanger Str. 52
D-88239 WANGEN
GERMANY
+49 7528 95 16 77
+49 7528 95 16 78

Mascot France
38 rue Leo Lagrange
94270 Le Kremlin Bicêtre
FRANCE
+33 1 46 58 71 85
+33 1 46 58 71 85