

Technical data **BOSCH**

Rated power input	2.300 W
Weight without cable	1,0 kg
Length	255 mm
Height	255 mm

Specifications, use

Working temperature	50 – 660 °C
Airflow	250 – 500 l/min
Infinitely variable temperature control +	
Cold-air setting, 50°C	+
Control, airflow	infinitely variable

Heat Gun GHG 660 LCD

