

Inductive Amplifiers



200GX

Description:

Like our tone generators, Tempo's inductive amplifiers are recognized as "Industry Standards" by field service professionals. Used in conjunction with any of our tone generators, our inductive amplifiers permit wire and cable identification without having to make direct metallic contact with the conductor. Powerful receiver gain permits accurate identification in even the most congested cable bundles and equipment rooms. Includes one each spare duckbill and metal tip.

The 200GX Inductive Amplifier offers the same exceptional qualities as Model 200EP, including an adjustable volume control for more precise identification when tone signal "bleed" is affecting the identification process, recessed tabs for buttset or headset connections and an LED display for visual signal strength indication - but now has a new, rugged, ergonomically-designed housing!

U.S. PAT. NO. 5,457,441; 5,574,769 and 5,577,099

Features:

- New rugged, ergonomically-designed housing
- Powerful 2" speaker
- One-Button operation
- Adjustable Volume Control
- LED for visual signal strength indication
- Recessed tabs for telephone test or headset connection
- Speaker bypass when using telephone test sets
- Improved tip design for better reception and lower risk of shorting terminals
- Battery operated (9V not included)