Data Sheet

HUBER+SUHNER

Coaxial Cable Connector 15_BMA-50-1-15/111_N

Description

Straight panel cable plug

Interface standards IEC 60169-33 MIL-STD-348A/321



Technical Data

Electrical Data

Impedance 50 Ω Interface frequency max. 18 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0027 kg

Environmental Data

Operating temperature -65 °C to 125 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Related Documents

 Outline drawing
 DOU-00009871

 Catalogue drawing
 DCA-00009873

 Assembly instruction
 DOC-0000185128

 Mounting hole
 DOU-00009871

Ordering Information

Single package 15_BMA-50-1-15/111_NE

Additional Information

Suitable cables EZ_47_TP_M17, SUCOFORM_47_CU

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.