

## Coaxial Cable Connector 16\_BNC-50-2-5/133\_N

### Description

Right angle cable plug

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0164 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00006459
Catalogue drawing	DOU-00006046
Assembly instruction	DOC-0000179255

### Ordering Information

Single package	16_BNC-50-2-5/133_NE
Bulk 100 pcs package	16_BNC-50-2-5/133_NH

### Additional Information

Suitable cables	K_02252_D, ENVIROFLEX_316_D, G_02232_D
-----------------	--