

Coaxial Cable Connector 11_BNT-50-2-1/103_N

Description

Straight cable plug

Interface standards
SUHNER-BNT



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	3 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0256 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00048065
Catalogue drawing	DOU-00007643
Assembly instruction	DOC-0000179264

Ordering Information

Single package	11_BNT-50-2-1/103_NE
----------------	----------------------

Additional Information

Suitable cables	G_02332
-----------------	---------

Remarks

Triaxial Connector