

Coaxial Cable Connector 11_MCX-50-2-15/133_N

Description

Straight cable plug

Interface standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0008 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00006602
Catalogue drawing DOU-00006606
Assembly instruction DOC-0000180174

Ordering Information

Bulk 100 pcs package 11_MCX-50-2-15/133_NH

Additional Information

Suitable cables ENVIROFLEX_316_D, K_02252_D, G_02232_D