

Coaxial Cable Connector 11_N-50-3-51/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 18 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | plugged |
| Outer contact | soldered |
| Weight | 0.0435 kg |

Environmental Data

| | |
|--|-----------------|
| Operating temperature | -55 °C to 70 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | Air Dielectric - Bead - PPH | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Catalogue drawing | DOU-00007863 |
| Assembly instruction | DOC-0000180866 |

Ordering Information

| | |
|----------------|---------------------|
| Single package | 11_N-50-3-51/133_NE |
|----------------|---------------------|

Additional Information

| | |
|-----------------|--|
| Suitable cables | SUCOFORM_141, EZ_141_TP_M17, MULTIFLEX_141 |
|-----------------|--|