Data Sheet



Coaxial Cable Connector 16_SMA-50-2-100/199_N

Description

Right angle cable plug

Interface standards SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 26.5 \ \text{GHz} \end{array}$

Mechanical Data

Centre contact plugged
Outer contact soldered
Weight 0.0056 kg

Environmental Data

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)

Related Documents

Outline drawingDOU-00072798Catalogue drawingDCA-00006235Assembly instructionDOC-0000229425

Ordering Information

Bulk 100 pcs package 16_SMA-50-2-100/199_NH

Additional Information

Suitable cables EZ_86_TP_M17, SUCOFORM_86, MULTIFLEX_86

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.